



NS&DNS CT Quick Install Instruction








Power Limit Configuration





CT is used for monitoring power transferring from inverter to grid. CT is connected to inverter, and firing line goes through it as Picture 1 showed below.




Picture 1





Open CT clamp and let the firing line which connected distribution box and grid go through it. There is K to L mark in CT which means the current direction. This direction cannot be wrong.




Current Direction $K \rightarrow L$ (Load \rightarrow Grid)

Picture 2





The white cable on CT connects to the No.1 port of 2pin connector, the black cable on CT connects to the No.2 port of 2pin connector. Please make sure the connection is right as Picture 3 & 4 showed below. Note: You will have to finish the connection of 2pin connector yourself on site.




Picture 3

Picture 4





When the screen displays the level 1 menu, please short press 'Enter' button to find out 'Power Limit OFF/ON' (the default setting is 'Power Limit OFF'), then long press the 'Enter' button to change 'Power Limit OFF' to 'Power Limit ON' as Picture 5 & 6 showed below.









Picture 6



After set 'Power Limit ON', short press 'Enter' button to find power limit rate then long press 'Enter' button to find percentage of power limit setting, setting rate is from 0%-100%. When you set the parameter, the relevant area will blink.


Note: Power to grid = Inverter output power * Limitation percentage.







After install CT and set power limit, you will see the inverter output power Pac = load power + limited max power as picture 8 showed below.







Q1: What is the tolerance for actual output of NS&DNS after set power limit percentage?

A1: Normally about 3% (Eg. GW1000-NS, set power limt 10% then maximum limited power is about 70W—130W).

Q2: If the power limit percentage can be set to 000% for NS&DNS?

A2: Yes . But there is still less power transfer to grid.

Q3: What is the shrink ratio for CT?

A3: 1:1000

Q4: What is the length for CT communication line?

A4: It should be within 5m which R&D tested.



Thanks

